

# EP10

The Barco EP10 –superb quality,outstanding performance,installation flexibility and ease of operation combined in one cost efficient solution for almost any application in Exhibition or Post Production.



**Product specifications****EP10****General specifications**

Technology	3 x 0.8" chip, DLP™
Resolution	1280 x 720
Contrast ratio	16 x 9
Brightness	3000 ANSI Lumens
Contrast	1200 : 1
Colors	4.4 m colors
Maximum screen size (diagonal)	10m (32ft)
Dimensions	282 x 605 x 694 mm (HxWxD)
Weight	25 kg
Power consumption	1000 W
Noise Level	42 dBA
Inputs	Native DVI, SDI, Component, S-Video, Composite Optional SDI
Anamorphic Lenses	Not required
Lamp	Size 2 x 250W UHP
Control	RS232 / 422
Special Features	16:9 DLP chip format Dual lamp operation

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.