

TransForm NDN-215 LITE

Networked Display Node



Barco's TransForm N system Networked Display Node is a powerful PC-based networked graphics processor. It is used in the networked visualization environment of a TransForm N system and can display encoded streams coming from the Gbit Ethernet/IP network. H-264, MPEG-4, V2D and ProServer represent just the top of a long list of supported codecs and streaming formats. Furthermore, the display controller also has a high-end graphics card to perform the rendering operations as are requested by the TransForm N management clients in the network.

High density content – Large display walls

The NDN-215 Lite Output nodes can display high density content and can drive up to sixteen HD displays with a single node. The unit supports multiple different types of displays including the whole range of Barco display solutions like RPC, LCD & LED. Managed by CMS inside the TransForm N system multiple NDN-215 Lite output nodes can be combined in a wall-cluster to show a composed synchronized picture on display walls of virtually unlimited size. The NDN-215 Lite offers a network based synchronization between the nodes suiting the majority of video-wall needs. Optional alternative a NDN-215 Pro can be selected for specific more advanced synchronization requirements.

Features:

- 4 DisplayPort 1.2 outputs
- Up to 4K-UHD resolution per output
- Universal IP video streaming decoding
- Network-based synchronization between multiple display nodes supporting the possibility to cluster up to 50 display nodes together driving a single wall
- Redundant network interface
- Silent operation in a compact and flexible form factor
- Mature Barco quality, robust and reliable

Product specificaties**TRANSFORM NDN-215 LITE****General specifications**

Geheugen	8 GB
Harde schijf	128 GB Solid-State Disk SSD
Netwerk	2x 1Gb/s LAN
Grafische kaart	Professional high-performance NVIDIA Quadro-series graphic card
Processor	Intel(R) Core(TM) i7 Quad core processor 3.2GHz (4.0GHz max. Turbo frequency)
Uitgang	4x Display Port 1.2 (supporting up to 4x 4K-UHD) 4x DVI-SL via included adapters (supporting up to 4x HD)
Invoer	H.264, MPEG-2/4, V2D, H.263, VNC, Pro-Server (see supported codec list)
Vormgeving	3U ½ 19" Rackmount housing
Afmetingen	133mm x 220mm x 300mm 5.24in x 8.66in x 11.81in
Voeding	100-240V, 5-3A, 50/60Hz
Energieverbruik	Typ. 110W max. 135W
Temperatuurbereik	0° -40°C 32° -104°F
Vochtigheid	Max. 80% (noncondensing)
Geluidsniveau	Max. 35dB(A) (measured at 1m/32.8ft distance at 22°/72)
Naleving	CE, CB, IEC 609501, ETL, FCC Class A Regulatory Model Id: NGP-210
Bestelgegevens	R9821018 NDN-215 LITE Display Node (no power cable) R9821018B NDN-215 LITE Display Node (US) R9821018F NDN-215 LITE Display Node (EU) R9821018G NDN-215 LITE Display Node (UK) R9821018X NDN-215 LITE Display Node (C13/C14) R9821099 Rackmount Kit for 2x NGP-210 R766042 Pedestal mount kit for NGP-210

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com