

# D320



**Product specificaties****D320****General specifications**

Invoer	4 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
Compatibiliteit	LED displays
Uitgang	DVI-A, DVI-D, RGB
Controle	<ul style="list-style-type: none"><li>- Scaler 4 input channels [Data-Video] fully scalable to desired output resolution</li><li>- Z-order Instant modification of Z-order control, for each output window</li><li>- Window positioning Intuitive positioning interface</li><li>- Connectors RS 232 [RJ11]</li></ul>
Effecten	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Bedrijfstemperatuur	0° <-> 45°
Vermogen	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Bestelgegevens	R9851570

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.