


F90-4K13

11,800 lumens, 4K UHD, DLP laser phosphor projector



- **Razor-sharp 4K images**
- **Ultimate installation flexibility, 24/7 operation**
- **Increased uptime, reduced costs**

The stunning image quality and laser phosphor light source of Barco's F90 projectors enable you to provide exceptional experiences while saving both time and money. Designed for installation in everything from high demanding visitor attractions to simulation applications that require 24/7 operation, the reliable F90 4K13 is equally suited for events, retail and advertising as well as boardrooms and auditoriums. Thanks to its 3D functionality, the projector is also perfectly fit for theme park dark rides and interactive experiences.

Superior image quality

The F90-4K13 delivers razor-sharp images at 4K UHD resolution with a high level of detail, and highly saturated colors that meet the Rec. 709 color space. Featuring an advanced optical design, this reliable projector provides a constant light output, for long-term, worry-free operation.

Unprecedented business value

The F90-4K13 projector enables you to increase uptime while driving costs down. Through its laser-phosphor light source and advanced cooling design, it provides up to 40,000 hours operating time without need for lamp changes - resulting in considerable cost-savings on maintenance and consumables.

Ultimate installation flexibility

This projector can run in any orientation, giving you more flexibility in projector location and orientation. Thanks to its wide array of high-resolution FLD and FLD+ lenses – from ultra-short throw (0.3:1) to long throw (9.75:1) – each providing a wide lens shift range, the F90-4K13 accommodates almost any projector configuration.

Product specifications**F90-4K13**

General specifications	
Projector type	Single chip DLP laser phosphor projector
Resolution	3,840 x 2,400 (4K UHD) / 2,560 x 1,600 (WQXGA native)
Brightness	11,700 center lumens* 10,500 ANSI lumens* 11,800 ISO lumens*
Contrast ratio	1,800:1 sequential, 10,000:1 dynamic*
Brightness uniformity	90%
Aspect ratio	16:10
Lens type	FLD+
Optical lens shift	Vertical up to 146%, depending on lens Horizontal up to 70%, depending on lens Motorized zoom and focus (+ lens memory FLDX lenses) Motorized lens shift (with position memory on all lenses)
Color correction	P7 RealColor™
CLO (constant light output)	Yes**
Light source	Laser phosphor
Light source lifetime	Up to 60,000 hours, depending on mode of operation
Sealed DLP™ core	Yes
Orientation	360° rotation, no restrictions
3D	Active stereoscopic 3D
Image processing	Embedded warp & blend engine
Keystone correction	Yes
Inputs	HDSDI, 2x DP 1.2, 2x dual link DVI-D, HDBaseT, HDMI2.0 (HDCP2.2, HDR10), RJ 45 Ethernet, DMX in/out***, RS232 in, 2x USB, 12v out
Input resolutions	Up to 4K UHD @ 60Hz / Up to 2,560 x 1,600 @ 120Hz refresh rates: 24Hz to 120Hz for WQXGA (2560x1600) and 24Hz to 60Hz for 4K/4KUHD (4096 x 2160/ 3860 x 2400)
Software tools	Projector Toolset
Control	IR, RS232, RJ45, XLR wired
Network connection	10/100 Ethernet, RJ45

Product specifications**F90-4K13**

Power requirements	110-240V / 50-60Hz
Power consumption	1500 W nominal, 2180 W maximum
BTU per hour	5100 BTU/h nominal, 7430 BTU/h maximum
Standby power	
Noise level (typical at 25°C/77°F)	38 dB(A)
Operating temperature	10 -45 °C (sea level)
Storage temperature	-20 to 60 °C
Operating humidity	20 -80% RH
Storage humidity	10 -90% RH
Dimensions (WxLxH)	575 x 730 x 295 mm / 22.64 x 28.74 x 11.61 in
Weight	44.5 kg / 98.1 lbs
Standard accessories	Power cord, wireless remote control
Certifications	CE, FCC Class A, cNemkoUS, CCC, EAC, KSA, KCC, RCM, UkrSEPRO
Warranty	Limited 3 years parts and labor. Extendable up to 5 years
24-7 documentation	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
Notes	* When measured with the FLD+ 1.7-2.5:1 (R9801216) on-axis and in Wide Angle position ** SW upgradable. Please contact an authorized Barco representative for details. *** When used in long-life mode, available through SW upgrade

Last updated: 13 Jun 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.