

BarcoGraphics 808s + Iris³

High Performance Graphics Projector



技术规格**BARCOGRAPHICS 808S + IRIS³****一般规格**

兼容性	Display compatibility from VHS Video up to 1600 by 1200 pixel workstations Horizontal autolock scan frequency range of 15-110 kHz Vertical scan frequency of 37-200 Hz autolock RGB bandwidth of 120 MHz Universal connection possibilities
对比度	>1000:1 (full white/full black)
光输出	1250 Lumen (at 10 % peak white)
屏幕尺寸	Min.: 1.4 m x 1.05 m (4.6' x 3.45') Max.: 6.0 m x 4.5 m (20' x 15')

生成于: 16 Mar 2023技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。