

# Argus

Display controller for easy video and data integration



## Product specifications

## ARGUS

### General specifications

Standard accessories	-keyboard/mouse extension for distances of up to 60 m -digital data cables for projector connection in copper and fiber optics, various lengths up to 100 m and beyond -Hermes DXD for controller system level redundancy
Dimensions	Argus processor <ul style="list-style-type: none"><li>• 19" Industrial case, height in rack unit: 4U</li><li>• Width case: 440 mm   17.32 in.</li><li>• Width with fixation: 482 mm   18.98 in.</li><li>• Depth case: 450 mm   17.72 in.</li><li>• Depth with handles: 502 mm   19.76 in.</li><li>• Height: 177 mm   6.97 in.</li><li>• Height with rubber feet: 183 mm   7.20 in.</li></ul> Argus omnibus <ul style="list-style-type: none"><li>• 19" Industrial case, height in rack unit: 6U</li><li>• Width case: 449 mm   17.68 in.</li><li>• Width with fixation: 449 mm   17.68 in.</li><li>• Depth case: 420 mm   16.54 in.</li><li>• Depth with handles: 461 mm   18.15 in.</li><li>• Height: 267 mm   10.51 in.</li><li>• Height with rubber feet: 270 mm   10.63 in.</li></ul>
Environmental Compliance	Operating Conditions 0 -40°C   30 -105°F at max. 80% humidity (non condensing)
Power consumption	Argus processor 300 W Argus omnibus 600 W
Power supply	100-240 V, 50/60 Hz
Weight	Argus processor approx 15.7 kg   34.6 lbs Argus omnibus approx 18.4 kg   40.6 lbs

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.