

ViewMAX

High Performance Down Converter



Product specificaties**VIEWMAX**

General specifications	
Analoge computervideo-ingang	High Resolution Video: RGB or Y,Pb,Pr, with horizontal scan rates up to 110KHz, resolutions up to 1600x1280 pixels. Input levels are independently programmable. Compatible with HDTV video Input Format: Interlaced or Non-Interlaced Sync Format: Sync-on-Video; Separate C or H, V Connectors: HD-15 Female, input and loop-through Termination: 75 Ohm or high impedance, switch selectable
Genlock-ingang	Format: NTSC or PAL video (composite video, black burst), 360° SCH phase adjustment Connectors: BNC input (Loop-through and termination switch available on ViewMAX with SDI option and ViewMAX-PRO) Termination: 75 Ohm or High impedance, switch selectable
Digitale video-ingang	(ViewMAX-DVI) Format: Digital Visual Interface (DVI) Connectors: DVI-D Female for both input and buffered loop-through output
Video-uitgang	Format: User-selectable 525/60 or 625/50, interlaced Composite Video: NTSC or PAL encoded composite, 1 v p-p into 75 ohms, BNC connector Component Video: User selectable format RGB Video: RS-170A or CCIR video, userselectable sync on video Betacam: Y,Pb,Pr, user-selectable sync on video Connectors: BNC S-Video (Y/C): DIN-4 connector Digital Video (SDI): Serial Digital Component 4:2:2 video output (optional on ViewMAX) Sync: TTL-level composite sync, BNC connector Output Resolution: 720 x 486 NTSC; 720 x 576 PAL
Video-ingang mixer	(ViewMAX-PRO) Format: 525/60 or 625/50 interlaced video Composite Video: NTSC or PAL video, BNC connector Component Video: Betacam (Y,Pb,Pr), BNC connectors S-Video: Y/C video, DIN-4 connector Digital Video (SDI): Serial Digital Component 4:2:2 video, BNC connector
Keying/mixing	(ViewMAX-PRO) Chroma or Luminance Keying
Controle	Front panel and RS-232/485 interfaces
Fysiek	Height: 1.75" (4.45 cm) Width: 17" (43.2 cm) or 19" (48.3 cm) with rack-mount option Depth: 10" (25.4 cm) Weight: 9 lbs (4.1 kg) Shipping Weight: 17 lbs (7.7 kg).
Ingangsvermogen	115 VAC/230 VAC, 50-60 Hz, 60W maximum
Milieuspecificaties	Temperature: 0-40 degrees C; Humidity: 0-95% noncondensing
Garantie	All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.